



▶ **Motorized Focus Drive MFD** for supplementary motorization of the Z-axis

<b>Resolution:</b>	typical 0,002 µm Depends on the speed reduction gear ratio of the microscope's fine focus, as well as the type of controller used!
<b>Motor:</b>	2-phase stepper motor
<b>Max. revolutions:</b>	60 rev. / s
<b>Material:</b>	aluminium
<b>Surface:</b>	anodic coating, black laquered
<b>Weight:</b>	ca. 790 g

**Order Information**

**MFD for Leica:**  
 DM2000 - DM3000: order no.: 31-54-501-0000  
 DM4000 - DM6000: order no.: 31-54-500-0000  
 DMI3000 - DMI6000: order no.: 31-54-500-0000

**MFD for Meiji Techno:**  
 MT 8530: order no.: 96-54-500-0000  
 MT5000 / MT6000: order no.: 96-54-500-0000

**MFD for Mitutoyo:**  
 FS-110: order no.: 00-54-501-0000

**MFD for Motic:**  
 BA 300: order no.: 00-54-500-0000

**MFD for Nikon:**  
 Epiphot 200, Epiphot 300, Optiphot, Optiphot 2, L150  
 Eclipse E400, E600, ME600L + D, TME200, TME300:  
 order no.: 45-54-500-0000  
 Eclipse E200: order no.: 45-54-501-0000  
 Eclipse TE2000: order no.: 45-54-502-0000  
 Eclipse TS100: order no.: 45-54-503-0000  
 Eclipse E600FN: order no.: 45-54-504-0000  
 Eclipse LV100D, LV150, 50i, 55i, 80i:  
 order no.: 45-54-505-0000  
 Eclipse L200, L300: order no.: 45-54-506-0000  
 Eclipse Ti: order no.: 45-54-507-0000

**MFD for Olympus:**  
 BX, BX41M, CKX41, GX, IX, MX50, MX61, SZX1:  
 order no.: 48-54-500-0000  
 AX70, IX61, BX51WI (back):  
 order no.: 48-54-502-0000  
 BH2: order no.: 48-54-501-0000  
 BX45: order no.: 48-54-503-0000  
 BX FM, BX51WI (vorn): order no.: 48-54-504-0000  
 SZX2: order no.: 48-54-505-0000

**Dimensions:**

